# PROCEEDINGS OF SPIE

# Nonlinear Frequency Generation and Conversion: Materials and Devices XX

Peter G. Schunemann Kenneth L. Schepler Editors

6–11 March 2021 Online Only, United States

Sponsored and Published by SPIE

Volume 11670

Proceedings of SPIE 0277-786X, V. 11670

SPIE is an international society advancing an interdisciplinary approach to the science and application of light.

Nonlinear Frequency Generation and Conversion: Materials and Devices XX, edited by Peter G. Schunemann, Kenneth L. Schepler, Proc. of SPIE Vol. 11670, 1167001 © 2021 SPIE · CCC code: 0277-786X/21/\$21 · doi: 10.1117/12.2596635

Proc. of SPIE Vol. 11670 1167001-1

The papers in this volume were part of the technical conference cited on the cover and title page. Papers were selected and subject to review by the editors and conference program committee. Some conference presentations may not be available for publication. Additional papers and presentation recordings may be available online in the SPIE Digital Library at SPIEDigitalLibrary.org.

The papers reflect the work and thoughts of the authors and are published herein as submitted. The publisher is not responsible for the validity of the information or for any outcomes resulting from reliance thereon.

Please use the following format to cite material from these proceedings: Author(s), "Title of Paper," in Nonlinear Frequency Generation and Conversion: Materials and Devices XX, edited by Peter G. Schunemann, Kenneth L. Schepler, Proc. of SPIE 11670, Seven-digit Article CID Number (DD/MM/YYYY); (DOI URL).

ISSN: 0277-786X ISSN: 1996-756X (electronic)

ISBN: 9781510641754 ISBN: 9781510641761 (electronic)

Published by **SPIE** P.O. Box 10, Bellingham, Washington 98227-0010 USA Telephone +1 360 676 3290 (Pacific Time) SPIE.org Copyright © 2021 Society of Photo-Optical Instrumentation Engineers (SPIE).

Copying of material in this book for internal or personal use, or for the internal or personal use of specific clients, beyond the fair use provisions granted by the U.S. Copyright Law is authorized by SPIE subject to payment of fees. To obtain permission to use and share articles in this volume, visit Copyright Clearance Center at copyright.com. Other copying for republication, resale, advertising or promotion, or any form of systematic or multiple reproduction of any material in this book is prohibited except with permission in writing from the publisher.

Printed in the United States of America by Curran Associates, Inc., under license from SPIE.

Publication of record for individual papers is online in the SPIE Digital Library.



**Paper Numbering:** A unique citation identifier (CID) number is assigned to each article in the Proceedings of SPIE at the time of publication. Utilization of CIDs allows articles to be fully citable as soon as they are published online, and connects the same identifier to all online and print versions of the publication. SPIE uses a seven-digit CID article numbering system structured as follows:

• The first five digits correspond to the SPIE volume number.

• The last two digits indicate publication order within the volume using a Base 36 numbering system employing both numerals and letters. These two-number sets start with 00, 01, 02, 03, 04, 05, 06, 07, 08, 09, 0A, 0B ... 0Z, followed by 10-1Z, 20-2Z, etc. The CID Number appears on each page of the manuscript.

## Contents

#### FREQUENCY COMBS AND SPECTROSCOPY

- 11670 04From optical parametric oscillation to frequency comb generation in whispering gallery<br/>resonators made of CdSiP2 [11670-2]
- 11670 05 A dual-comb spectrometer for trace gas analysis in the mid-infrared [11670-3]

#### INFRARED GENERATION

- 11670 08Seeded optical parametric generation in CdSiP2 pumped by a nanosecond pulsed, MHz<br/>repetition rate Raman fiber amplifier at 1.24 µm [11670-6]
- 11670 OA A widely tunable difference-frequency-generation laser for high-resolution spectroscopy in the 667–865 cm<sup>-1</sup> range [11670-8]
- 11670 0B Advances in 2 μm polarization-maintaining thulium-doped Q-switched fiber lasers for frequency conversion into the mid-IR [11670-9]
- 11670 OC Spatial structure and simulations of midwave infrared ultrashort pulse laser frequency conversion in polycrystalline chalcogenide optical materials [11670-10]
- 11670 0D High-pulse-energy, Q-switched Ho<sup>3+</sup>:YAG laser for mid-infrared optical parametric oscillator pumping [11670-11]
- 11670 OE Q-switched, high average output power Tm<sup>3+</sup>:Ho<sup>3+</sup>-codoped triple-clad fiber laser for nonlinear frequency conversion [11670-12]

#### **NEW CONCEPTS OF NONLINEAR OPTICS**

- 11670 OF First demonstration of nonlinear interferometry in the terahertz frequency range [11670-13]
- 11670 0G Widely tunable second harmonic amplification by noncollinear phase matching in bulk birefringent materials [11670-14]
- 11670 OH Coherent combining of optical parametric oscillators: challenges and experimental results [11670-15]
- 11670 0K Mechanisms of beam clean up at Raman conversion of multimode radiation in graded-index fibers [11670-18]

#### NEW NONLINEAR MATERIALS

- 11670 OPChalcopyrite and chalcogenide crystals for terahertz radiation generation and detection<br/>(Invited Paper) [11670-23]
- 11670 0Q Measurement of temperature dependent refractive indices of GaN and 4H-SiC [11670-24]

### NONLINEAR WAVEGUIDE DEVICES

- 11670 OR Mid-infrared parametric generation in OP-GaAs waveguides pumped by a femtosecond erbium-doped fluoride fiber laser [11670-25]
- 11670 0U Second-order nonlinear effects in InGaAsP waveguides for efficient wavelength conversion to the mid-infrared [11670-28]
- 11670 0V Efficient difference frequency generation for quantum frequency conversion in a multimode PPLN-waveguide [11670-29]

#### OPTICAL PARAMETRIC AMPLIFICATION

- 11670 0W Few-cycle, μJ-level pulses beyond 5 μm from 1-μm-pumped OPA's based on non-oxide nonlinear crystals (Invited Paper) [11670-30]
- 11670 0X High power 9 μm source for spectroscopy and HHG [11670-31]
- 11670 OY High-power OPCPAs at 1450–2400 nm wavelength [11670-32]
- 11670 0Z 1 MHz dual channel, CEP stable, few-cycle OPCPA at 800nm and >1.7µm wavelength [11670-33]

#### **OPTICAL PARAMETRIC DEVICES AND APPLICATIONS**

- 11670 10 Nonlinear interferometers for Fourier-transform infrared spectroscopy with visible light [11670-34]
- 11670 11 Mid-IR difference-frequency generation in OP-GaAs inside the cavity of a narrow-band nanosecond PPLN optical parametric oscillator [11670-35]
- 11670 13 6 μm pulsed OP-GaAs OPO laser for unambiguous water ice detection on the Moon and other planetary bodies [11670-37]
- 11670 14 kW-class nanosecond pulsed polarized MOPA laser at 2050 and 2090 nm [11670-38]
- 11670 15 Advances in the spectral coverage of tunable continuous-wave optical parametric oscillators [11670-39]

### STIMULATED RAMAN AND SUPERCONTINUUM GENERATION

| 11670 16 | Towards remote chemical sensing: backward-generated coherent anti-Stokes Raman scattering [11670-40]   |
|----------|--|
| 11670 17 | IR-supercontinuum seeded efficient two-stage transient stimulated Raman amplification in KGW with pulse compression [11670-41]   |
| 11670 18 | Spatiotemporal guided bullets in multimode fiber [11670-42]  |
| 11670 19 | Supercontinuum generation in orientation-patterned gallium phosphide [11670-43]  |
| 11670 1B | Femtosecond supercontinuum source in the C-band with equalized spectra through evolutionary strategy based adaptive optimization of nonlinear spectral broadening [11670-45] |
|          | VISIBLE-UV GENERATION  |
| 11670 1D | High power continuous laser at 461 nm based on a frequency-doubling linear cavity [11670-47]   |
| 11670 1E | Updated Sellmeier equations of β-BaB <sub>2</sub> O <sub>4</sub> [11670-48]  |
| 11670 1G | Walk-off compensated nonlinear crystal stacks for efficient harmonic wavelength conversions [11670-50]   |
| 11670 1H | Alternating dual-wavelength second harmonic generation at 532 nm using a Y-branch distributed Bragg reflector diode laser [11670-51]   |
|          | POSTER SESSION   |
| 11670 1K | Accurate Sellmeier equations for AgGaS <sub>2</sub> in the 0.565-10.6321 $\mu m$ spectral range [11670-54]   |
| 11670 10 | Walk-off effect in nonlinear crystals suitable for UVC generation [11670-58]   |